
SERIES 16 45° GREEN DOUBLE SET SCREW PANEL MOUNT - FEMALE

PS45FRBG | [Pass & Seymour](#)

FEATURES & BENEFITS

Pass & Seymour cam-type devices are built with top-quality materials for enhanced durability and service life, along with increased insulation protection for safety. Our angled receptacle offerings are ideal for supplying temporary electrical distribution for film and other entertainment production, theme parks, fairs, carnivals, concert venues, arenas and convention centers, mining and construction, marine shipbuilding and repair and more.

WARNING: This product can expose you to chemicals including DEHP and lead, which are known to the State of California to cause cancer, and DEHP and lead, which are known to the State of California to cause birth defects or other reproductive harm. For more information, go to www.P65Warnings.ca.gov.



- **Type 3R Rated** for indoor and outdoor use.
- **Solid one-piece brass contacts** provide superior and consistent connection under the most extreme conditions.
- **Housing is made of Santoprene®** for outstanding impact and chemical resistance.
- **Intermateable and compatible** with competitive cam-type products.
- **Can be retrofitted** to existing locations and power distribution systems.
- **Brass eyelets** for #10-32 mounting through bolts (bolts not provided).
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Green

Number Of Poles: 1

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No. 65-93

CSA Standard: Yes
UL Listing No: UL498
UL Standard: Yes

DIMENSIONS

Cable Diameter Range: 2/0 - 4/0
Depth (US): 2.045"
Height (US): .500"
Length (US): 2.250"

TECHNICAL INFORMATION

Amps: 400A
NEMA Rating: 3R
Volts: 600VAC

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

