
SERIES 16 IN-LINE CONNECTORS

PS40FBBK | [Pass & Seymour](#)



FEATURES & BENEFITS

400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Black

WARNING: This product can expose you to chemicals including DEHP and lead, which are known to the State of California to cause cancer, and DEHP and lead, which are known to the State of California to cause birth defects or other reproductive harm. For more information, go to www.P65Warnings.ca.gov.



- Thermoplastic elastomer housing for outstanding impact and chemical resistance
- Exceptional seal for maintaining NEMA Type 3R and 4 integrity
- Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product
- Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity
- Heavy-duty hex set screws allow greater termination torque
- Copper wire provides quality strain relief
- Copper shim bundles wire strands to reduce "splaying."

SPECIFICATIONS

GENERAL INFO

Color: Black

Type: In line connectors female

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: cCSAus File Number LR81290

CSA Standard: Yes

cULus: Yes

UL Listing No: E111198

UL Standard: Yes
UN SPSC: 39121403

DIMENSIONS

Length (US): 6.80"

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

