

---

## 20A, 125V WATERTIGHT STRAIGHT BLADE PLUG, YELLOW

14W33 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Rated watertight for 1,500 psi high-pressure hosedown, P&S plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.



- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
- Devices resist high-pressure hose down of 1,500 psi.
- Color-coded sealing bushings provided for a large range of cord diameters.
- Large ribs on body for a superior grip when mating.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow  
Type: Plug  
Features: Watertight  
Number Of Poles: 2  
Number Of Wires: 3  
Special Features: Watertight

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: LR701645  
CSA Listed: Yes  
CSA Standard: Yes  
Federal Spec: Yes

UL Listing No: E146159  
UL Standard: Yes  
UN SPSC: 39121402

#### **DIMENSIONS**

Diameter (US): 1.63"  
Length (US): 2.68"

#### **TECHNICAL INFORMATION**

Amps: 20A  
NEMA Configuration Number: 5-20  
NEMA Rating: 4X/6P  
Volts: 125V

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

