



20A, 250V WATERTIGHT STRAIGHT BLADE PLUG, BLACK

14W48BK | [Pass & Seymour](#)

FEATURES & BENEFITS

Rated watertight for 1,500 psi high-pressure hosedown, P&S watertight plugs and connectors feature multiple seals to ensure protection against the environment. Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
- Devices resist high-pressure hose down of 1,500 psi.
- Color-coded sealing bushings provided for a large range of cord diameters.
- Large ribs on body for a superior grip when mating.
- All black construction.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Black
Type: Plug
Features: Watertight
Number Of Poles: 2
Number Of Wires: 3
Special Features: Watertight

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listed: Yes
CSA Standard: Yes
cULus: Yes
Federal Spec: Yes

DIMENSIONS

Diameter (US): 1.63"
Length (US): 2.68"

TECHNICAL INFORMATION

Amps: 20A
NEMA Configuration Number: 6-20
NEMA Rating: 4X/6P
Volts: 250V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

