



## 15A, 250V WATERTIGHT SINGLE RECEPTACLE, YELLOW

60W49 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Straight Blade Watertight Single Receptacle, 15amp 250volt, NEMA Configuration 6-15, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, & corrosion.



- Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.
- Spring loaded flip covers provide protection when device is not in use.
- Stainless steel hinge spring and pin for corrosion resistance.
- For Covering Patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow  
Type: Receptacles  
Features: Watertight  
Number Of Poles: 2 Pole  
Number Of Wires: 3 Wire  
Special Features: Watertight,NEMA

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 No. 42M  
CSA Standard: Yes  
UL Listing No: E146159  
UL Standard: Yes  
UN SPSC: 39121402

#### DIMENSIONS

Length (US): 1.25"

#### TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 6-15

NEMA Rating: 4X/6P

Volts: 250V

Volts (AC): 250

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

