



## HARD-USE SPEC GRADE PLUG LOAD CONTROLLABLE RECEPTACLE, 20A, 125V, IVORY

TR5362CHI | [Pass & Seymour](#)

### FEATURES & BENEFITS

Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with NEC®, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.



- Can be wired to any number of system-based or stand-alone plug load control solutions.
- Factory-broken split-circuit tab allows for 50% plug load control to be achieved in one duplex receptacle.
- Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- 8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory

Type: Receptacles

Duty: Hard Use Commercial Spec Grade

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 No. 42  
CSA Listed: Yes  
CSA Standard: File No. LR16063  
Federal Spec: Yes  
UL Listing No: UL498  
UL Standard: File No. E140596  
UN SPSC: 39121406

#### **DIMENSIONS**

Depth (US): 0.780"  
Height (US): 3.281"  
Width (US): 1.322"

#### **TECHNICAL INFORMATION**

Amps: 20A  
NEMA Configuration Number: 5-20R  
Volts: 125V  
Volts (AC): 125  
Capacity: Duplex  
Grade Type: Commercial

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

