



## TR5252LA TAMPER-RESISTANT DUPLEX RECEPTACLE, BACK & SIDE WIRE, 15A, 125V, LIGHT ALMOND

TR5252LA | [Pass & Seymour](#)

### FEATURES & BENEFITS

Tamper-Resistant Specification Grade Duplex Receptacle, Back & Side Wire, 15amp 125volt, Light Almond.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- High impact-resistant nylon face and thermoplastic back body.
- Back and side wire capability
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Type: Receptacles  
Features: Tamper-Resistant  
Number Of Poles: 2  
Number Of Wires: 3  
Special Features: Back, Side Wire, Tamper-Resistant  
Style: Duplex

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 No.42

CSA Standard: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406

#### **DIMENSIONS**

Depth (US): .65"  
Height (US): 3.28"  
Width (US): 1.32"

#### **TECHNICAL INFORMATION**

Amps: 15A  
NEMA Configuration Number: 5-15R  
Volts: 125V  
Volts (AC): 125  
Capacity: Duplex  
Grade Type: Specification

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

