



USB CHARGER WITH HOSPITAL GRADE TAMPER-RESISTANT SINGLE RECEPTACLE, WHITE

TR8201USBW | [Pass & Seymour](#)

FEATURES & BENEFITS

2 Standard type A USB's, 2.1 A or 2100mA, 10.5 watts. Combination with Hospital Grade Tamper-Resistant 15 A AC Single Receptacle, White.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



PRODUCT ENVIRONMENTAL PROFILE

- **2.1 A USB type A receptacle charges faster than other USB receptacles** eliminates the need for bulky AC adapters.
- **Compact Design** Tamper-Resistant receptacle and two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.
- **Back and side wire terminals** accommodates #14 AWG - #10 AWG stranded and solid wire.
- **Tamper-Resistant, patented shutter system** prevents improper insertion of foreign objects. Meets 2011 National Electrical Code® Tamper-Resistant requirements.
- **Stainless steel auto-ground clip** assures positive ground.
- **Zink-plated ground terminal screw**
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Discontinued: Yes

Color: White

Type: Tamper-Resistant

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No.42 & No. 223

CSA Standard: Yes

ETL Listing No: 4001804

ETL Listed: Yes

Federal Spec: Yes

UL Listing No: Complies with test requirements UL 498, UL 1310

DIMENSIONS

Depth (US): 1.31"

Height (US): 4.18"

Width (US): 1.60"

TECHNICAL INFORMATION

Amps: 15A

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No