



## DOUBLE POLE, SINGLE PHASE AC MANUAL MOTOR CONTROLLER

7832MD | [Pass & Seymour](#)

### FEATURES & BENEFITS

Double Pole, Single Phase AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.



- High Horsepower rating of 20HP
- Gull-wing shaped brass terminal pressure clamps
- Constructed of glass-reinforced thermoplastic
- UL508 and cULus Listing of individual device and assembled device within enclosure
- Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing
- External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### SPECIFICATIONS

#### GENERAL INFO

Number Of Poles: 2

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.23 14  
CSA Standard: Yes  
UL Listing No: 508  
UL Standard: Yes

UN SPSC: 39121512

**DIMENSIONS**

Depth (US): 1.80"

Height (US): 5.75"

Width (US): 4.50"

**TECHNICAL INFORMATION**

Amps: 30A

Volts: 600VAC

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

