



INDUSTRIAL SPEC GRADE TURNLOK® 20A NON-NEMA FLANGED INLET, GRAY

7408SS | [Pass & Seymour](#)

FEATURES & BENEFITS

Rely on Pass & Seymour Turnlok® portable power solutions for all your demanding jobsite applications that require temporary power.



- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

SPECIFICATIONS

GENERAL INFO

Color: Gray

Number Of Wires: 4

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121403

DIMENSIONS

Depth (US): 1.65"

Diameter (US): 2.87"

TECHNICAL INFORMATION

Amps: 20A

Volts: 120/208V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

