
29W09 WATERTIGHT NEMA 4X/6P LOCKING CONNECTOR

29W09 | [Pass & Seymour](#)



FEATURES & BENEFITS

Watertight Connector, 30amp 3^Y 120/208V, Non-NEMA Configuration, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.



- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down to 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

SPECIFICATIONS

GENERAL INFO

Color: Yellow
Type: Connector
Features: Watertight
Number Of Poles: 3
Number Of Wires: 3
Special Features: Watertight, Non-Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 42M
CSA Standard: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121403

CONSTRUCTION INFORMATION

Material 1: Rubber

DIMENSIONS

Diameter (US): 2.76"

Length (US): 4.88"

TECHNICAL INFORMATION

Amps: 30A

Material: Rubber

NEMA Rating: 4X/6P

Volts: 3°Y 120/208V

Volts (AC): 3°Y 120/208V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

