



## 69W09 TURNLOK WATERTIGHT SINGLE RECEPTACLE, YELLOW

69W09 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Turnlok Watertight Single Receptacle, 30amp 3°Y 120/208 volt, Non NEMA Configuration, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, & corrosion.

- Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.
- Spring loaded flip covers provide protection when device is not in use.
- Stainless steel hinge spring and pin for corrosion resistance.
- For Covering Patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow

Type: Receptacles

Features: Turnlok® Watertight

Number Of Poles: 4 Pole

Number Of Wires: 4 Wire

Special Features: Non Grounding, Turnlok®, Watertight

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42M

CSA Standard: Yes

UL Listing No: E146159

UL Standard: Yes

UN SPSC: 39121402

#### DIMENSIONS

Length (US): 1.89"

#### TECHNICAL INFORMATION

Amps: 30A

NEMA Rating: 4X/6P

Volts: 120/208V

Volts (AC): 120/208

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

