

---

## VELOCITY™ DVI-D™ MALE TO HDMI[R] FEMALE INLINE ADAPTER

40746 | [C2G](#)



---

### FEATURES & BENEFITS

Use this adapter to provide a pure digital, high-definition video connection! You'll see the purity of the original signal with absolutely no picture degradation! Fully tested and absolutely guaranteed. Gold-plated contacts deliver worry-free performance, and make this adapter an ideal choice to connect digital source components to DVI-equipped display devices! Ideal for satellite, DVD player, HDTV, plasma, LCD and DLP applications. Don't compromise your high-definition video signal; use the right interconnects! [\*] Download a version of the technical specifications of this product on the Support tab

- Connect a HDMI cable to a DVI port
- Supports up to a 1080p resolution
- Compact design

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black  
Product Series: Velocity  
Type: HDMI Adapters and Couplers  
Component Type: Adapters

#### DIMENSIONS

Height (US): 0.5"  
Length (US): 2"  
Width (US): 1.75"  
Weight: 0.072 lbs

#### CORD INFORMATION

Connector Type End One: HDMI Female  
Connector Type End Two: DVI-D Single Link Male

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA