

---

## 50 OHM BNC F/F INLINE ADAPTER

02030 | [C2G](#)



---

### FEATURES & BENEFITS

We offer a complete solution for ethernet coaxial connections. From the most common crimp and twist-on male connectors, to the hard-to-find pass-through terminated t-connector, we have it all. If you don't see what you need, just contact us.

#### Features

- Easily extend BNC cable runs by combining two cables
- No signal loss
- Lifetime warranty

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Silver

Type: RF Adapters and Couplers

Component Type: Adapters

#### DIMENSIONS

Height (US): 0.25"

Length (US): 1.25"

Width (US): 0.25"

Weight: 0.01 lbs

#### CORD INFORMATION

Connector Type End One: BNC Female

Connector Type End Two: BNC Female

Cord Length US: 0

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: Buy American Act Compliant