

---

## TRULINK®; 4-PORT VGA/USB 2.0 KVM SWITCH

35567 | [C2G](#)



---

### FEATURES & BENEFITS

The TruLink® 4-Port VGA/USB 2.0 KVM offers a quick and easy way to eliminate clutter from your desktop. This switch allows you to control four computers with just one keyboard, mouse, and VGA monitor. Connect the switch to your computers via USB and VGA using the included cables.

- Supports video resolutions up to 2048 x 1536 pixels.
- Features autoscan and autoswitch
- Offers overcurrent protection
- Compatible with USB 2.0 specification

#### Signal Specifications

- Video Signal Supported - VGA
- Maximum Resolution Supported - 2048 x 1536
- Operating Systems Supported - Windows® 98/SE/2000/ME®/XP®/Vista®/7, Mac® O.S 9.0 or later versions
- USB Specification Supported - USB 2.0
- Switching Methods - Keyboard Hotkeys, Push button, Auto-Scan

#### Power Adapter Specifications

- Power Input - 100-240V 50/60Hz, 0.4A
- Power Output - 5V, 2.0A
- Power Cable Length - 5ft
- Power Pin Diameter - 5.5mm
- Center Pin Polarity - Positive

#### Physical Characteristics

- Number of Computers Supported - 4
- Computer Connection Ports - HD15 (VGA) Male x 4, USB B Female x 4
- Console Ports - HD15 VGA Female, USB A Female x 2 (keyboard and mouse)
- USB Hub - USB A Female x 2
- Included Cables - HD15 (VGA) M/F and USB A to B Combo Cable x 4
- Cable Length - 1.8m
- Housing Material - Metal
- Dimensions - 200.6 x 81.28 x 43.18mm

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black  
Number Of Ports: 4  
Product Series: TruLink  
Type: VGA Switches