
10FT PREMIUM HD15 MALE TO RGBHV (5-BNC) MALE VIDEO CABLE

07573 | [C2G](#)

FEATURES & BENEFITS

This cable is constructed from premium quality 75 Ohm mini coax wire to ensure a crisp monitor image. Low loss 75 Ohm impedance and polyethylene dielectric provide an accurate picture resolution and color. Each wire is shielded with 85% copper braid that is soldered 360[D] to the connector shell to create a shielding solution for a vivid, noise-free image. Color-coding of the five separated monitor signals provides easy identification of red, green, and blue leads with horizontal and vertical sync. Fully molded connectors provide excellent strain relief to keep your cable intact.

- 28 AWG tinned-copper coax conductor delivers quality video
- PVC jacket is flexible for easy installation
- Aluminum undermold and braided shield assists in reducing EMI/RFI interference to meet FCC requirements

SPECIFICATIONS

GENERAL INFO

Color: Grey
Type: VGA to BNC Adapters
Component Type: Cables

DIMENSIONS

Height (US): 2.75"
Length (US): 7.5"
Width (US): 5.25"
Weight: 0.95 lbs

CORD INFORMATION

Connector Type End One: VGA Male
Connector Type End Two: BNC RGBHV Male
Cord Length US: 10'

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA