



## 50FT 3.5MM STEREO AUDIO CABLE WITH LOW PROFILE CONNECTORS M/M - IN- WALL CMG-RATED

40109 | [C2G](#)

### FEATURES & BENEFITS

Audio installations in educational and commercial settings often require in-wall rated cable. Our CMG-rated line was specifically engineered to meet this requirement while overcoming common challenges faced by installers in these environments. Low-Profile connectors (1.41in total depth) save valuable space in the gang box. This cable is constructed from 22 AWG twisted pair wire and drain wire. The entire cable is foil shielded to ensure signal integrity. CMG rated cables meet many NEC requirements for Communications Cables General Purpose In Wall Use. Our cables meet the following ratings: CMG, FT4, CM, CL3, CL2, CMX, CL3X, and CL2X. Always check with your local authority on building requirements to verify cable requirements before beginning any installation.

#### Features

- In-wall, CMG-Rated jacket
- 22 AWG conductor construction
- Low-profile connectors
- Supports a Stereo Audio signal

### SPECIFICATIONS

#### GENERAL INFO

Color: Black  
Type: 3.5mm Audio Cables  
Component Type: Cables

#### DIMENSIONS

Height (US): 1.25"  
Length (US): 8"  
Width (US): 7.5"  
Weight: 0.886 lb

#### CORD INFORMATION

Connector Type End One: 3.5mm Stereo Male  
Connector Type End Two: 3.5mm Stereo Male  
Cord Length US: 50'

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA