



6FT VELOCITY[™] 3.5MM M/M MONO AUDIO CABLE

40620 | [C2G](#)

FEATURES & BENEFITS

This cable is specifically designed to provide quality signal transfer for mono audio and data transfer applications. It features two 27 AWG oxygen-free copper conductors, a drain wire, an aluminum foil shield to prevent unwanted EMI/RFI interference, and fully molded, gold-plated connectors providing strain relief for a quality connection.

SPECIFICATIONS

GENERAL INFO

Color: Blue
Product Series: Velocity
Type: 3.5mm Audio Cables
Component Type: Cables

DIMENSIONS

Height (US): 0.5"
Length (US): 7"
Width (US): 5"
Weight: 0.2 lb

CORD INFORMATION

Connector Type End One: 3.5mm Mono Male
Connector Type End Two: 3.5mm Mono Male
Cord Length US: 6'

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA