



## 25FT VELOCITY[™] 3.5MM M/F MONO AUDIO EXTENSION CABLE

40628 | [C2G](#)

---

### FEATURES & BENEFITS

This cable is specifically designed to extend the signal for mono audio and data transfer applications. It features two 27 AWG oxygen-free copper conductors, a drain wire, an aluminum foil shield to prevent unwanted EMI/RFI interference, and fully molded, gold-plated connectors providing strain relief for a quality connection. A common use for this cable is to extend the 3.5mm serial data cable that connects your digital camera to your PC.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Blue  
Product Series: Velocity  
Type: 3.5mm Audio Cables  
Component Type: Cables

#### DIMENSIONS

Height (US): 1.25"  
Length (US): 6"  
Width (US): 6.5"  
Weight: 0.76 lb

#### CORD INFORMATION

Connector Type End One: 3.5mm Mono Male  
Connector Type End Two: 3.5mm Mono Female  
Cord Length US: 25'

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA