
12FT PRO-AUDIO XLR MALE TO XLR FEMALE CABLE

40060 | [C2G](#)

FEATURES & BENEFITS

Use this XLR to XLR cable to connect unbalanced sources to balanced XLR inputs. This pro-audio cable is made from 22 AWG twisted pair audio cable under an aluminum foil shield and 60% copper braid for maximum shielding from noise. The highly flexible 7mm PVC jacket reduces the risk of the cable kinking and damaging the conductors. Bright nickel plating on solid brass connectors resists wear from reconfiguring and moving equipment from one venue to another. Spring strain relief on the 1/4in plug and a chuck strain relief inside the XLR reduce the effects of age on the solder joints and contacts.

Features

- 22 AWG conductor construction
- Foil and braided shield to protect from interference
- Highly flexible jacket
- Nickel-plated connectors

SPECIFICATIONS

GENERAL INFO

Color: Black
Type: Pro Audio Cables
Component Type: Cables

DIMENSIONS

Height (US): 0.75"
Length (US): 8"
Width (US): 5"
Weight: 0.54 lb

CORD INFORMATION

Connector Type End One: XLR 3-pin Male
Connector Type End Two: XLR 3-pin Female
Cord Length US: 12'

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA