



100FT VELOCITY[™] RCA STEREO AUDIO CABLE

29103 | [C2G](#)

FEATURES & BENEFITS

Don't let your interconnects be the weak link in your audio system chain! This audio cable offers excellent sound quality because its bonded construction design delivers a neat, easy connection of audio signals. Twisted pair oxygen-free copper wire and foamed PE dielectric are optimized for audio signal transmission. The 100% foil shield protects the audio signals from electromagnetic interference (EMI) and radio frequency interference (RFI). Color-coded molded connectors and an ultra-flexible jacket enable easy installation. 24K gold-plated heavy duty contacts ensure a lifetime of performance.

Features

- Color coded, fully molded connectors
- Ultra flexible PVC jacket
- 24K gold plated contacts
- Tinned Oxygen Free Copper

SPECIFICATIONS

GENERAL INFO

Color: Blue
Product Series: Velocity
Type: RCA Audio Cables
Component Type: Cables

DIMENSIONS

Height (US): 3"
Length (US): 9"
Width (US): 8.25"
Weight: 3.45 lb

CORD INFORMATION

Connector Type End One: RCA Stereo Audio Male
Connector Type End Two: RCA Stereo Audio Male
Cord Length US: 100'

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA