

---

## 12FT VELOCITY[™] RIGHT ANGLED SUBWOOFER CABLE

29180 | [C2G](#)



---

### FEATURES & BENEFITS

Overcome difficult connections due to confined spaces between a receiver and entertainment units, wall or rack with Velocity Right Angled Subwoofer cables. Twisted pair oxygen-free copper wire and foamed PE dielectric fight noise and hum, and are optimized for bass signal transmission. Oxygen-free copper conductors deliver awesome impact and bass detail. The low loss 100% foil and spiral-wound oxygen-free copper (OFC) shielding protects the important bass signals from electromagnetic interference (EMI) and radio frequency interference (RFI). A tough, ultra-flexible jacket and 24K gold-plated heavy duty contacts ensure a lifetime of performance.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Blue  
Product Series: Velocity  
Type: Subwoofer Cables  
Component Type: Cables

#### DIMENSIONS

Height (US): 1"  
Length (US): 7"  
Width (US): 5"  
Weight: 0.32 lb

#### CORD INFORMATION

Connector Type End One: RCA Line-level Audio Male  
Connector Type End Two: RCA Line-level Audio Male  
Jacket Rating: Standard Non-Rated  
Cord Length US: 12'

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA