



## 1000FT RG6/U QUAD SHIELD IN-WALL COAXIAL CABLE

43065 | [C2G](#)

---

### FEATURES & BENEFITS

Our RG6/U quad shield cable is ideal for antenna, cable television and satellite installations. This cable has an 18 AWG copper clad steel center conductor surrounded by a foam polyethylene dielectric. A bonded aluminum foil and 60% aluminum braid over another foil and 40% aluminum braid provide 100% shield coverage. Use for CL1, CL2, CM, CMX and CMG installations. Swept tested to 3 GHz to ensure performance at applicable frequencies. To help you keep track of cable used, the cable jacket is sequentially marked every two feet.

- Inner Conductor: 1/1.02 mm (18 AWG) Copper Clad Steel
- Insulation: 4.57mm foam PE
- Outer Conductor: Al/P-Foil (bonded) + 0.12mm x 80 Al wire braiding + Al/P/Al-Foil + 0.12mm x 48 Al wire braiding
- Coverage: 60% + 40%
- Sheath: 7.62mm black PVC (C/UL CMG CL2)

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black  
Type: RG6 Cable