
6FT VELOCITY[™] COMPOSITE VIDEO CABLE

27231 | [C2G](#)

FEATURES & BENEFITS

The Velocity video cable ensures vivid picture quality and maximum detail from your composite video sources. This cost-effective high-performance cable has a real performance advantage over cheap "included in the box" cables included with many consumer electronics products. The low loss 75 Ohm oxygen-free copper conductor and foamed PE dielectric maintain proper characteristic impedance, and guarantee that you will experience all the picture quality and performance your equipment can deliver. An oxygen-free copper (OFC) braided shield protects against electromagnetic interference (EMI) and radio frequency interference (RFI). Fully molded connectors provide excellent strain relief. A flexible jacket and 24-karat gold-plated heavy duty contacts ensure long-lasting quality.

SPECIFICATIONS

GENERAL INFO

Color: Blue
Product Series: Velocity
Type: Composite Video Cables
Component Type: Cables

DIMENSIONS

Height (US): 0.25"
Length (US): 5.5"
Width (US): 5"
Weight: 0.13 lb

CORD INFORMATION

Connector Type End One: RCA Composite Video Male
Connector Type End Two: RCA Composite Video Male
Cord Length US: 6'

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA