



10FT PRO SERIES SINGLE LINK DVI-D[™] DIGITAL VIDEO CABLE M/M - IN-WALL CL2- RATED

41231 | [C2G](#)

FEATURES & BENEFITS

The new Pro Series commercial grade CL2 cables offer true digital performance while meeting the highest standards in building code requirements for in-wall installations. Available for HDMI[R], DVI and DVI+3.5mm audio signals, these cables can meet the demands of virtually any commercial installation. By supporting resolutions of 1080p for displays and up to 1920 x 1200 pixels for computers, and with lengths ranging from 6 to 50 feet, the Pro Series is the ideal connectivity solution for A/V equipment used in classrooms or conference rooms. 24k gold-plated connectors prevent metal corrosion, resulting in the optimal signal transfer for the highest picture and sound quality. Shielded 24AWG copper conductors protect against EMI and RFI to ensure uninterrupted performance. High quality materials and construction, along with rigorous factory testing and a full lifetime warranty, guarantee long-term, dependable performance. *CL2 is equivalent to FT4 rating in Canada, while CMP is equivalent to FT6.

Please Note: Does not support analog video; only supports digital video signal. [*] Download a version of the technical specifications of this product on the Support tab [F

path="/toolkits/ProSeries_Digital_Plenum_CL2_Toolkit.zip">[IMG src="/icons/prodDesc/toolkit.gif" title="Toolkit" align="left"> [/F]

SPECIFICATIONS

GENERAL INFO

Color: Black
Product Series: Pro Series
Type: DVI-D Single and Dual Link Cables
Component Type: Cables

DIMENSIONS

Height (US): 3"
Length (US): 8"
Width (US): 8"
Weight: 1.488 lbs

CORD INFORMATION

Connector Type End One: DVI-D Single Link Male
Connector Type End Two: DVI-D Single Link Male

Cord Length US: 10'

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA