



0-10V LED/FLUORESCENT DIMMER, TRI-COLOR

RH4FBL3PTC | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

Designed to handle 0-10 volt dimming in fluorescent and LED fixtures.

radiant® Screwless Wall Plate not included.



- Part of the all-new radiant™ collection.
- For use with 0-10V, 4 wire, 120V 10A/277V 5A LED and fluorescent dimming drivers/ballasts.
- Convenient operation combines ON/OFF paddle switch with separate slider for dimming control.
- Preset, single pole and 3-way operation.
- White LED glows when dimmer is OFF for easy location in the dark.
- Wider slide control for easier dimming operation.
- Constant memory returns lights to previous level after a power failure.
- No derating required for one- and two-gang applications.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Tri-Color (Ivory, White, Light Almond)

Number Of Poles: Single Pole/3-Way

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No. 184

CSA Standard: Yes

cULus: Yes

UL Standard: Yes

CONSTRUCTION INFORMATION

Component 4: 78500705597

DIMENSIONS

Depth (US): 1.25"

Height (US): 4.25"

Width (US): 1.75"

TECHNICAL INFORMATION

NEMA Rating: Yes

Rating (A): 0-10V

Volts: 0-10V

Volts (AC): 120VAC 10A / 277VAC 5A

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA