



## 120V CFL/LED DIMMER, GRAPHITE

RHCL453PGCCV4 | [radiant](#)

### FEATURES & BENEFITS

Replace any existing outlet with the modern appeal and added energy savings of this graphite finish, 120V CFL/LED Dimmer. The graphite finish is designed to complement the beauty of black stainless-steel appliances and satin or matte black fixtures and hardware.

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

This dimmer is compatible with CFL/LED dimmable bulbs (except 0-10V LED drivers).

radiant® Screwless Wall Plate not included.



- Replace any standard switch with ease.
- Combines ON/OFF paddle switch with separate slider for dimming control and convenient operation.
- White LED glows when dimmer is OFF for easy location in the dark.
- Constant memory returns lights to previous level after a power failure.
- Adjustment dial allows users to adjust the bottom of the dimming range for a wide range of CFL and LED bulbs.
- Single pole or 3-way operation for greater convenience and installation flexibility.
- No derating required in multi-gang applications.
- Rating: 450W LED; CFL; 700W Incandescent; 120VAC, 60Hz.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Graphite

Type: CFL/LED

Number Of Poles: Single Pole/3-Way

Style: Rocker

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 184

CSA Standard: Yes

cULus: Yes

UL Standard: Yes

#### CONSTRUCTION INFORMATION

Component 4: 78500717374

#### DIMENSIONS

Depth (US): 1.25"

Height (US): 4.25"

Width (US): 1.75"

#### TECHNICAL INFORMATION

Volts: 120

Volts (AC): 120 VAC, 60Hz

Watts: 450/701

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA