



SINGLE POLE/3-WAY FAN SPEED CONTROL

RHDH163PBCCCV4 | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes. Enjoy quiet fan speed control of your home ceiling fan. Designed to coordinate with bronze and nickel fixtures and hardware.

radiant® Screwless Wall Plate not included.

- Helps control fan speed without the need for pull-chains from the fan itself.
- De-hummer feature virtually eliminates fan motor "hum" for quiet fan speed control.
- White LED glows when fan control is OFF for easy location in the dark.
- Constant memory returns the fan to previous level after a power failure.
- Ideal for use with residential ceiling fans.
- Single pole and 3-way operation.
- Works with standard 3-way switches and wiring.

SPECIFICATIONS

GENERAL INFO

Color: Bronze, Nickel
Number Of Poles: Single Pole/3-Way
Special Features: De-Hummer

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 184
CSA Standard: Yes
cULus: Yes
UL Standard: Yes
UN SPSC: 39121502

CONSTRUCTION INFORMATION

Component 4: 78500715836

DIMENSIONS

Depth (US): 1.25"

Height (US): 4.25"

Width (US): 1.75"

TECHNICAL INFORMATION

Amps: 1.6A

Volts: 120V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA