



BROADCAST INTERCOM ROOM STATION, NICKEL

IC7000-NI | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

The Broadcast Intercom Room Station provides easy and accessible whole-home communication and offers absolute convenience and enhanced peace of mind. Communicating with all intercom stations throughout the home, the IC7000-NI also allows for answering the front door from any room of the house as well as features room monitoring - ideal for keeping an ear on infants or elderly parents.

radiant® Screwless Wall Plate not included.

- Part of the radiant® collection.
- Compact, single gang intercom unit providing effortless, simultaneous communication between rooms
- Features hard-buttons for monitoring and mute functions
- Simple RJ45 plug design for easy installation and troubleshooting
- Available in White, Light Almond

SPECIFICATIONS

GENERAL INFO

Discontinued: Yes

Cable Type: Cat 5e, or Cat 6, or better

Color: Nickel

Available Colors: White, Light Almond, Nickel

Size: 3.38" x 4.38" x 7.125"

Typical Applications: Part of the Selective Call Intercom System

Type: Residential

Special Features: Hi-resolution LCD display, supports up to 3 simultaneous conversations

CONSTRUCTION INFORMATION

Component 4: 80442812068

DIMENSIONS

Height (Metric): 85.85mm
Height (US): 3.38"
Length (Metric): 181mm
Length (US): 7.125"
Width (Metric): 111.25mm
Width (US): 4.38"
Weight: 0.45 lbs / 0.204 kg

TECHNICAL INFORMATION

Compatible Power Supplies: 24 VDC external power supply
Current Max: 0.25mA max.
Humidity: Up to 90% Relative Humidity (non-condensing)
Jack Connectors: RJ45
Mounting: Mounts in a standard electrical wall box or mud ring
Operating Temperature (Celsius): 0°C ~ 55°C
RatedVoltage: +24 VDC (+/- 1.25 VDC)