



IC7001-NI |

FEATURES & BENEFITS

SPECIFICATIONS

GENERAL INFO

Color: Nickel

CONSTRUCTION INFORMATION

Material 1: ABS Plastic/Steel

DIMENSIONS

Overall Dimensions (US): 4 7/8" x 4 7/8"

Weight: 1 lb

CORD INFORMATION

Pinning:

1. 24 VDC

OUT

2. GND

3. Audio (+)

4. COMM A

5. COMM B

6. Audio (-)

7. NOT

USED

8. NOT

USED

TECHNICAL INFORMATION

Cat5 Cable Rating: CAT5 UTP, 4 pair solid conductor (24 AWG)

Humidity: Up to 90% RH (non-condensing)

Material: ABS Plastic/Steel

Operating Temperature (Celsius): 0 to 55°C

Power Requirements: +24 Vdc, +/-1.25 Vdc, 0.25 A max
QLink Selective Call Ports: RJ-45
Storage Temperature: -55 to 75°C