



COMBINATION TAMPER-RESISTANT 15A SELF-TEST SINGLE-POLE SWITCH/GFCI, WHITE

1597SWTTRWCCD4 | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

The self-test GFCI conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

Make sure you can spot ground fault trips quickly and resolve them easily with GFCI Receptacles installed in the living space.

radiant® Screwless Wall Plate not included.

For detailed GFCI receptacle information, visit our [GFCI Headquarters](#).

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Part of the radiant® collection
- Switch rating: 15A, 120VAC, Single Pole
- Single-gang device provides up-and-down switching combined with GFCI safety features. Ideal for remodeling, and perfect for bath and kitchen vents
- Protects children: patented shutter system helps prevent improper insertion of foreign objects meeting National Electrical Code® Tamper-Resistant requirements
- Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the trip indicator light (red LED) flashes to signal that the GFCI should be replaced
- Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected
- Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box
- Feed-thru wiring configuration allows GFCI to protect downstream receptacles
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly
- Side or internal screw-pressure-plate back wire with #10-#14 AWG solid or stranded copper wire and two back wire holes per terminal

- Mounting screws are shipped captive in the device for easier installation
 - Dual-direction test and reset button colors match the device face
 - 10kA short circuit rating
 - 20 Amp feed-thru capacity
-

SPECIFICATIONS

GENERAL INFO

Color: White

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

cULus: Yes

Federal Spec: Yes

UL Standard: UL498

CONSTRUCTION INFORMATION

Component 4: 78500713574

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15R

Volts: 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA