



## SPEC-GRADE 15A SELF-TEST DUPLEX GFCI, WHITE, 100-COUNT BULK PACKAGE

1597W100 | [radiant](#)

### FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

The self-test GFCI conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock™ Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

Make sure you can spot ground fault trips quickly and resolve them easily with GFCI Receptacles installed in the living space.

radiant® Screwless Wall Plate not included.

For detailed GFCI receptacle information, visit our [GFCI Headquarters](#).



- Part of the radiant® collection
- Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the trip indicator light (red LED) flashes to signal that the GFCI should be replaced
- Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box
- Feed-thru wiring configuration allows GFCI to protect downstream receptacles
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly
- Side or internal screw-pressure-plate back wire with #10-#14 AWG solid or stranded copper wire and two back wire holes per terminal
- Mounting screws are shipped captive in the device and wall plate for easier installation
- Dual-direction test and reset button colors match the device face
- Supplied with matching TP wall plate
- 10kA short circuit rating
- 20 Amp feed-thru capacity
- Product packaged in quantities of 100.

## SPECIFICATIONS

### GENERAL INFO

Color: White

### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

cULus: Yes

Federal Spec: Yes

UL Standard: UL498

### TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15R

Volts: 125

### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA