



TAMPER-RESISTANT RECEPTACLE, WHITE

885TRW | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® Screwless Wall Plate not included.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Replaces any standard outlet with ease.
- Meets NEC® Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects—now with black "invisi-shutters" for an invisible effect preferred by end users.
- High-impact resistant thermoplastic construction and long-term blade retention for extended service life.
- Superior protection than traditional outlet caps or protection plates.
- Low-profile face; ultrasonic welding of face to back body for greater reliability.
- Side-access push wire release; side wire terminal screws #12 – #14 AWG solid wire; push wire terminals accept #14 AWG solid cooper wire only.
- Longer tri-drive screws and quick loop wiring aid for easier #12 AWG looping.
- Extra-large circuit break-off tabs.
- Captivated mounting screws offer hassle-free installation.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 No.42
CSA Standard: Yes
cULus: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121704

CONSTRUCTION INFORMATION

Component 4: 78500730477

DIMENSIONS

Depth (US): 1"
Height (US): 3.812"
Width (US): 1.29"

TECHNICAL INFORMATION

Amps: 15A

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA