



WEATHER-RESISTANT RECEPTACLE, WHITE

885TRWRW | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® Screwless Wall Plate not included.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Residential Weather-Resistant Receptacles are Tamper-Resistant as required by National Electrical Code.
- Listed to the Weather-Resistant supplement of UL498, meeting demanding UL requirements including: Ultraviolet light exposure test; Cold impact test; Accelerated aging test; Stringent material requirements for current-carrying parts, wire binding screws and mounting straps to ensure superior corrosion resistance.
- WR markings on face per UL Weather-Resistant requirements.
- Patented internal shutter system lets plugs in, but keeps keys and other objects out with automatic shutters that block access.
- Side wire accepts #12 – #14 AWG solid wire.
- Push wire accepts #14 AWG solid only. Low profile face.
- Traditional contoured face.
- High-impact resistant thermoplastic construction.
- Safer and more effective than plastic outlet caps.
- TR markings identify devices as Tamper-Resistant.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White

Number Of Poles: 2

Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No.42

CSA Standard: Yes

cULus: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121704

CONSTRUCTION INFORMATION

Component 4: 78500724171

DIMENSIONS

Depth (US): 1"

Height (US): 3.31"

Width (US): 1.29"

TECHNICAL INFORMATION

Amps: 15A

Volts: 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

