



15A SINGLE POLE SWITCH, NICKEL

TM870NICC10 | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® Screwless Wall Plate not included.



PRODUCT
ENVIRONMENTAL PROFILE

- Replaces any standard switch with ease.
- Smooth paddle action.
- High-impact resistant thermoplastic construction.
- Side wire terminal screws #12 – #14 AWG solid wire; push wire terminals accept #14 AWG solid cooper wire only.
- Narrow back body leaves more room for wires in the electrical box.
- Captivated mounting screws offer hassle-free installation.
- Coordinate your USB charger with a radiant screwless wall plate.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Nickel
Number Of Poles: Single Pole
Style: Rocker

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 111

CSA Standard: Yes
UL Listing No: UL20
UL Standard: Yes
UN SPSC: 39121704

CONSTRUCTION INFORMATION

Component 4: 78500702105

DIMENSIONS

Depth (US): 1.27"
Height (US): 4.19"
Width (US): 1.43"

TECHNICAL INFORMATION

Amps: 15A
Volts: 120/277

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: Buy American Act Compliant