



8802S-FC12 OMNIBOX SERIES FIRE CLASSIFIED 2-GANG FLOOR BOX

8802S-FC12 | [Wiremold](#)

FEATURES & BENEFITS

2-Gang Fire Classified Steel Floor Box. Adjustment range over deck of 2" (51mm) minimum to 6-1/2" (165mm) maximum. One 1 1/4" (32mm) and One 2" (51mm) conduit feed openings. Box Capacity - 58.5 cubic inches each gang. This floor box preserves up to a 3-hour fire rating of floors in which it has been installed.

SPECIFICATIONS

GENERAL INFO

Product Series: FCFB
Component Type: Boxes
Knockout Size: 1 1/4" - 2"

CONSTRUCTION INFORMATION

Installation Location: Above-Grade

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MULTIPLE

Buy American Act Status: Exception

Note: While most parts within this series comply with the BAA's Country of Origin requirements, some do not. For a complete list of all parts and their respective Country of Origin, refer to the "Series Part List-COO" under "Supporting Documents" on the "Resources" tab.