

2" (51MM) IPS NO. 2 DUCT, 24" (610MM) SPACING

2-24x2 |



FEATURES & BENEFITS

Factory installed round preset duct with internal threads to accept standard connectors. 10' (3m) standard length, 16 gauge galvanized steel construction with continuous seam weld. Preset I.D. is 2" (51mm) conduit



- This product meets the material restrictions of RoHS

SPECIFICATIONS

GENERAL INFO

Product Series: Walkerdect Pro Series
Component Type: Duct Systems

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status:
Note: UNITED STATES OF AMERICA

