
OUTDOOR GROUND BOX, L14-30R, GRAY

XB814CL1430GY | [Wiremold](#)



FEATURES & BENEFITS

The Gray Outdoor Ground Box cover assembly is prewired with a single NEMA L14-30R corrosion-resistant Locking receptacle.

CAUTION: All ground box electrical circuits must be protected by a Ground Fault Circuit Interrupter upstream from the ground box.

NOTE: Cover must be closed while in use. Use only molded plug and cord assemblies that are rated for outdoor use.

NOTE: Maximum length of plug allowed at end of cord is 3" (76mm).



- Only outdoor ground box that is cULus listed to UL50E Type 6P (NEMA 6P) and IP68 requirements while in use
- ADA compliant
- Outdoor-rated construction
- Keeps receptacles and connections dry even when submerged

SPECIFICATIONS

GENERAL INFO

Color: Gray

Product Series: Outdoor Ground Box

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UL Listing No: E486738

DIMENSIONS

Overall Dimensions (US): 14" x 8" x 7"

Product Weight (US): 9 lbs

TECHNICAL INFORMATION

NEMA Rating: 6P

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No