

---

## OUTDOOR GROUND BOX, L15-20R

XB814CL1520 | [Wiremold](#)



---

### FEATURES & BENEFITS

The Outdoor Ground Box cover assembly is prewired with a single NEMA L15-20R corrosion-resistant Locking receptacle.

**CAUTION:** All ground box electrical circuits must be protected by a Ground Fault Circuit Interrupter upstream from the ground box.

**NOTE:** Cover must be closed while in use. Use only molded plug and cord assemblies that are rated for outdoor use.

**NOTE:** Maximum length of plug allowed at end of cord is 3" (76mm).



- Only outdoor ground box that is cULus listed to UL50E Type 6P (NEMA 6P) and IP68 requirements while in use
- ADA compliant
- Outdoor-rated construction
- Keeps receptacles and connections dry even when submerged

---

### SPECIFICATIONS

#### GENERAL INFO

Available Colors: Brown, Black, and Gray

Product Series: Outdoor Ground Box

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

UL Listing No: E486738

#### DIMENSIONS

Overall Dimensions (US): 14" x 8" x 7"

Product Weight (US): 9 lbs

**TECHNICAL INFORMATION**

NEMA Rating: 6P

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA

Buy American Act Status: No