



OUTDOOR GROUND BOX 30A, 250V TURNLOK[®] LOCKING RECEPTACLE L6-30R, BLACK

XB814CL630BK | [Wiremold](#)

FEATURES & BENEFITS

The black Outdoor Ground Box cover assembly is prewired with (1) 30A L6-30R 240V corrosion-resistant duplex receptacles.

CAUTION: All ground box electrical circuits must be protected by a Ground Fault Circuit Interrupter upstream from the ground box.

NOTE: Cover must be closed while in use. Use only molded plug and cord assemblies that are rated for outdoor use.

NOTE: Maximum length of plug allowed at end of cord is 3" (76mm).

- cUL Coming Soon
- UL listed to UL50E Type 6P (NEMA 6P) and IP68 requirements while in use
- ADA compliant
- Outdoor-rated construction
- Keeps receptacles and connections dry even when submerged

SPECIFICATIONS

GENERAL INFO

Color: Black

Product Series: Outdoor Ground Box

DIMENSIONS

Overall Dimensions (US): 14" x 8" x 7"

TECHNICAL INFORMATION

NEMA Rating: 6P

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No