



AMDTP-412 - AMDTP-4 SERIES ALUMINUM TELE-POWER POLE

AMDTP-412 | [Wiremold](#)

FEATURES & BENEFITS

Two-compartment pole (power and communications). Nominal material thickness .050" (1.8mm). Length: 10' 5" (3.2m). Factory wired with 20A 125V fed-spec general grade duplex style receptacles. An opening for communication and a 1/2" (12.7mm) hole for power is provided at top. The 8" (203mm) cover at top front of pole is removable for making power wiring connections. Communication KOs provided for RJ11/RJ45 and modular furniture connectors. Mounting hardware, entrance end fitting, and ceiling trim plates furnished. Anodized aluminum finish. Available in standard length of 12' 5" (3.8m). NOTE 1: Custom colors, other lengths (20' (6.1m) max.) or additional circuits are available on custom orders. Consult factory for more information. Can be factory- or field-wired with many commercially available devices. NOTE 2: Add the suffix "-C" for the cord-ended version (10' (3.0m) cord). Cord-ended version AVAILABLE IN CANADA ONLY.



SPECIFICATIONS

GENERAL INFO

Product Series: Tele-Power

DIMENSIONS

Height: 12' 5" [3.8m]

TECHNICAL INFORMATION

Material: Aluminum

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant



