



CABINETMATE PLUG-IN OUTLET CENTER UNIT / 120V/20A/48" LONG/10 O/L /15' CORD/TWIST LOCK PLUG

4810ULBD20R-TL | [Wiremold](#)

FEATURES & BENEFITS

Ten 20A outlets with t-slots, 15' (4.6m) cord. Length 48" (1.2m). Receptacle center-to-center 4" (101mm). 20 Amp unit with a 20A resettable circuit breaker. Available in straight blade or Locking Plug.

*California Residents: This product can expose you to chemicals including Di(2-ethylhexyl)phthalate [DEHP], which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to: www.P65Warnings.ca.gov

SPECIFICATIONS

TECHNICAL INFORMATION

Amps: 20
Mounting: 0U
RatedVoltage: 120V
Number Of Circuits: 1
Receptacle Type: NEMA
Network Monitoring: No
Surge Suppression: Computer Grade
Number Of Outlets: 10

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

