



CABINETMATE PLUG-IN OUTLET CENTER UNIT / 120V/20A/77" LONG/12 O/L /6' CORD/TWIST LOCK PLUG

7712ULBC20R-TL | [Wiremold](#)

FEATURES & BENEFITS

Twelve 20A outlets with t-slots, 6' (1.8m) cord. Length 77" (2m). Receptacle center-to-center 6" (152mm). 20 Amp unit with a 20A resettable circuit breaker. Units available with straight blade or Locking Plug.

SPECIFICATIONS

TECHNICAL INFORMATION

Amps: 20
Mounting: 0U
RatedVoltage: 120V
Number Of Circuits: 1
Receptacle Type: NEMA
Network Monitoring: No
Surge Suppression: Computer Grade
Number Of Outlets: 12

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

