



CABINETMATE PLUG-IN OUTLET CENTER  
UNIT / 120V/20A/77" LONG/12 O/L /6'  
CORD/TWIST LOCK PLUG

7712ULBC20R-TL | [Wiremold](#)

### FEATURES & BENEFITS

Twelve 20A outlets with t-slots, 6' (1.8m) cord. Length 77" (2m). Receptacle center-to-center 6" (152mm). 20 Amp unit with a 20A resettable circuit breaker. Units available with straight blade or Locking Plug.

### SPECIFICATIONS

#### TECHNICAL INFORMATION

Amps: 20  
Mounting: 0U  
RatedVoltage: 120V  
Number Of Circuits: 1  
Receptacle Type: NEMA  
Network Monitoring: No  
Surge Suppression: Computer Grade  
Number Of Outlets: 12

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

