



## POWER COMMANDER PDU/120V/30A/SINGLE PHASE/18 PCS 5- 20R O/L/AMMETER

3B53B2-1-AM | [Wiremold](#)

---

### FEATURES & BENEFITS

Two circuits with two 15A resettable circuit breakers and two lighted LCD digital ammeters. Eighteen 20A outlets with T-slots, black housing. 12' (3.6m) cord. Length 48" (1.3m).

---

### SPECIFICATIONS

#### TECHNICAL INFORMATION

Amps: 30  
Mounting: 0U  
RatedVoltage: 120V  
Number Of Circuits: 2  
Receptacle Type: NEMA  
Network Monitoring: No  
Number Of Outlets: 24

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

