



**POWER COMMANDER
PDU/120V/40A/SPLIT-PHASE (2 X 20A)/18
PCS 5-20R O/L AMMETER**

4B53B2-2-AM | [Wiremold](#)

FEATURES & BENEFITS

Two circuits with two 20A resettable circuit breakers and two lighted LCD digital ammeters. Eighteen 20A outlets with T-slots, black housing. 12' (3.6m) cord. Length 54" (1.4m).

SPECIFICATIONS

TECHNICAL INFORMATION

Amps: 40
Mounting: 0U
RatedVoltage: 120V
Number Of Circuits: 2
Receptacle Type: NEMA
Network Monitoring: No
Number Of Outlets: 18

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

