
24S7224GBX99IV STEEL PLUGMOLD®; MULTIOUTLET STRIP

24S7224GBX99IV | [Wiremold](#)



FEATURES & BENEFITS

6' Steel Plugmold Multioutlet Strip with 3 duplex receptacles spaced at 24", GB

- **Steel Raceway.** Provides superior strength for any dry location installation with greater wire capacity than V2000.
- **Ivory ScuffCoat finish.** Durable scratch resistant finish.
- **Removable cover.** Allows easy access to wiring for changes or additions.
- **Full range of fittings.** Provides a complete wiring solution.
- **Single-and-dual-gang boxes.** Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.
- **Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 20A, 120V receptacles.** Ideal for short runs requiring additional outlets in electrically busy areas.
- **Single or alternating circuit.** Meets virtually any circuit requirement.
- **Choice of receptacle spacing.** Center spacing between receptacles of 6", 12" and 18".
- **Simplex receptacle.** More spacing options available.
- **Duplex receptacle.** Aesthetically pleasing, functional 20A duplex for the 24S (2400) Series.
- **Customization available.** All products can be modified to accommodate virtually any application.

SPECIFICATIONS

Video: Installation Guidelines for Plugmold® in the City of Chicago.

For the Complete Product List for this series, click this link:

GENERAL INFO

Product Series: 2400PM

Component Type: Raceway Base & Cover

TECHNICAL INFORMATION

Material: Steel

Capacity: Single-Channel

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

