



3' ALL USB STEEL PLUGMOLD® MULTIOUTLET SYSTEM

20USB312 | [Wiremold](#)

FEATURES & BENEFITS

3' (914mm) length with 12" spacing. USB is 2.4 Amps (shared between two ports) 5VDC. .040" (1.0mm) steel housing. Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. Each USB module provides 2 ports with 2.4 Amps of shared charging. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

- **USB charging.** Dual-port charging modules share 2.4 amps of charging capacity and can charge multiple phones, tablets or other mobile devices at the same time.
- **Multiple colors and finishes.** Painted finishes of black, gray, ivory, and white, as well as stainless steel versions integrate easily with any room decor.
- **Compact design.** Low-profile design installs in tight locations while offering multiple USB charging connections. Receptacle spacing accommodates bulky AC adapters.

SPECIFICATIONS

GENERAL INFO

Available Colors: Black, Gray, Stainless, Ivory, White

Product Series: 20USB

Component Type: Raceway Base & Cover

TECHNICAL INFORMATION

Material: Steel

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

