



## PLUGMOLD NM2000 WITH SNAPICOIL HARNESS

NM20GB12 | [Wiremold](#)

### FEATURES & BENEFITS

Nonmetallic Plugmold with Snapicoil harness. 48' in length with receptacles spaced 12" on center. Nonmetallic Plugmold has a textured ivory finish. For use with 15 amp circuit.

- **Nonmetallic, lightweight with snap-on cover.** Speeds installation; provides easy access to wiring for changes or additions.
- **Tapered profile design with textured ivory finish.** Blends with surroundings in office, display space, dorm rooms and residential locations.
- **Full range of fittings.** Facilitates easy installation of wiring for whatever the job: communication workstation outlets, receptacles, switches and more. Over lapping fittings permit neat butting to raceway.
- **Factory wired harness available with duplex receptacles on multiple spacings.** Maximum power distribution to the point of use.
- **NEMA heavy duty duplex receptacles independently tested to Fed. Spec. WC596G performance criteria.** Enhanced product quality ensures dependable performance.
- **Snapicoil harnesses of prewired receptacles in 48' and 50'.** Eliminates the need for multiple splicing, speeding up installations on long runs.
- **Snapicoil harnesses offer a choice of receptacle spacing.** Center spacing between receptacles of 12", 18" and 30".
- **Field replaceable surge module.** No need to remove the raceway cover to splice in a replacement receptacle. Field changes and maintenance are quick and easy.
- **Customization available.** All products can be modified to accommodate virtually any application.

### SPECIFICATIONS

Video: Installation Guidelines for Plugmold® in the City of Chicago.

**For the Complete Product List for this series, click this link:**

#### GENERAL INFO

Product Series: NM2000

#### TECHNICAL INFORMATION

Material: Nonmetallic

Capacity: Single-Channel

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA

