



Ortronics

Signamax 065-79SXMG-H Compatible 1000Base-SX SFP Transceiver (MMF, 850nm, 550m, LC Duplex, DDM, I-Temp)

Part No. 065-79SXMG-H-L



Signamax 065-79SXMG-H Compatible 1000Base-SX SFP Transceiver (MMF, 850nm, 550m, LC Duplex, DDM, I-Temp)

## Features & Benefits

### Guaranteed Compatible

In System tested in over 90 OEM switches, routers and servers.

### 99.98% Reliability Rate

Functionally, optically and environmentally tested to exact specifications.

### Industry Leading Lifetime Warranty

For more information by product line, visit our Warranty page.

### 98% On-Time Delivery Rate

Extensive inventory guarantees same day shipping.

### Full Service Technical Support

Call, chat, email or meet for expert optical connectivity support.

## Specifications

### General Info

Product Line	Ortronics	Country Of Origin	China
Type	Transceiver		

### Technical Information

Fiber Optic Cable Type	Multimode	Operating Temperature Min	-40 C
Operating Temperature Max	85 C	Connector Type	LC Duplex
Wavelength	850nm	Form Factor	SFP